



Main

Range of product	Acti 9
Product name	Acti 9 IHH
Device short name	IHH
Product or component type	Mechanical time switch
Number of channels	1
Function available	Manual time changeover

Complementary

Device application	Building
Load type	10 parallel-corrected fluorescent tube (58 W) 15 parallel-corrected fluorescent tube (40 W) 230 V AC halogen lamp (1000 W) 230 V AC incandescent lamp (1000 W) 3 parallel-corrected fluorescent tube (100 W) 7 fluocompact lamp (11 W) 7 fluocompact lamp (15 W) 7 fluocompact lamp (20 W) 7 fluocompact lamp (7 W)
Cycle duration	7 days
Measurement accuracy	+/- 1 s/day
Maximum number of switchings	42 on - 42 off
Minimum interval duration	2 h
Type of setting	Manual time changeover
Measurement accuracy	+/- 1 s/day 20 °C
Power consumption in VA	2.5 VA
Maximum switching current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] rated operational voltage	230 V AC +/- 10 % at 50/60 Hz
Battery life	10 year(s)
Backup time	100 h time and program saving
Mounting support	DIN rail
9 mm pitches	2
Colour tint	White (RAL 9003)
Connections - terminals	Screw terminals
IP degree of protection	IP20 B
Width	18 mm
Height	90 mm
Depth	66 mm
Net weight	0.101 kg

Environment

Ambient air temperature for operation	-10...50 °C
IP degree of protection	Terminals: IP20 B

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------