



Main

Product name	Easy56
Product or component type	Socket-outlet
Device short name	EY56SO420
Plug, socket category	Low voltage
Poles description	3P + E
Network type	AC
Outlet standard	Australian/New Zealand

Complementary

Mounting mode	Surface mounted
Plug, socket, control station shape	Straight
[In] rated current	20 A
Pin number	4 pins
Shape of pin	Tubular
[Ue] rated operational voltage	500 V
Network frequency	50 Hz
Material	Polycarbonate: cover
Contacts material	Pins: brass
Connections - terminals	Screw terminals 2.5...6 mm ² rigid or stranded cable
Wire stripping length	16 mm
Net weight	0.471 kg
Height	101 mm
Width	101 mm
Depth	101 mm
Colour	Grey (RAL 7035)

Environment

Standards	AS/NZS 3123
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Ambient air temperature for storage	-25...75 °C

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------