



Main

Range of product	Acti 9
Product name	Acti 9 iPB
Product or component type	Push-button
Device short name	IPB
Standards	IEC 60669-1 IEC 60947-5-1



Complementary

Contacts type and composition	1 NC
[Ie] rated operational current	20 A
[Ue] rated operational voltage	250 V AC
Control type	1 push-button red
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Comb busbar and distribution block compatibility	Upside: Clario Upside: Libro Upside: ProDis
9 mm pitches	2
Height	82 mm
Width	18 mm
Depth	71.5 mm
Colour	White
Electrical durability	AC-22: 30000 cycles AC 50/60 Hz
Connections - terminals	Staggered tunnel terminal1 cable(s) 0.5 mm ² rigid Staggered tunnel terminal1 cable(s) 0.5 mm ² flexible Staggered tunnel terminal1 cable(s) 0.5 mm ² flexible with ferrule Staggered tunnel terminal2 cable(s) 2.5 mm ² rigid Staggered tunnel terminal2 cable(s) 2.5 mm ² flexible Staggered tunnel terminal2 cable(s) 2.5 mm ² flexible with ferrule
Wire stripping length	9 mm
Tightening torque	1 N.m

Environment

Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------