



### Main

Range of product	Series 12M
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

### Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Mounting support	skirt
Fixing mode	By screws
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	29 mm
Length	63 mm
Width	43 mm
Number of poles	1

### Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

### Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.