



Main

Range of product	Resi MAX
Product type	Meter box
Enclosure type	Plain door enclosure
Device application	Metering Distribution
Targeted country	Tasmania


Complementary

Enclosure mounting	Semi flush Surface
Number of modules	21
Provided equipment	Earth and neutral grid assembly DIN rail Fascia plate Enclosure
Protection device type	Miniature circuit breaker (MCB) - 63 A - 1P - 6 kA
Cable entry	Knock-out top and bottom Knock-out rear
Type of door	Ventilated removable door with door retainer
Door opening side	Right
Lock type	Cam lockable
Material	Iron (galvanised)
Surface finish	Epoxy powder coat
Width	464 mm
Height	860 mm
Depth	282 mm
Colour	Beige

Environment

IP degree of protection	IP23
Standards	AS/NZS 3000

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.