



Main

Range	Clipsal Iconic
Product or component type	USB charger
[Ue] rated operational voltage	220/240 V AC 50 Hz
Integrated connection type	1 USB 2.0 type A 5 V DC, maximum load current: 1.5 A
Maximum load current with 2 outputs used simultaneously	1.5 A

Complementary

Device mounting	Flush
Device presentation	Mechanism
Colour tint	Vivid white
Fixing mode	Clipped
Sale per indivisible quantity	1
Ambient air temperature for operation	0...45 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	5...90 %
Number of terminals	1 with cable end
Height	48 mm
Width	27 mm
Depth	56 mm
Embedding depth	55 mm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.