



Main

Range	Clipsal Iconic
Product or component type	Dimmer
Device presentation	Mechanism
Dimmer type	Universal
Colour tint	Vivid white (VW)
Type of packing	Box
Load type	Dimmable LED - 300 W - 240 V AC Low voltage halogen lamp with iron core transformer - 300 W - 240 V AC Incandescent - 300 W - 240 V AC

Complementary

Range compatibility	Clipsal Iconic
Control type	Push-button ControlLink
Fixing mode	Clip-in
Surface finish	Glossy
Ambient air temperature for storage	0...60 °C
[Ue] rated operational voltage	220...240 V AC 50 Hz
Function available	Brightness adjustment
Protection type	Short-circuit
Ambient air temperature for operation	0...45 °C
Relative humidity	5...90 %
Connections - terminals	Screw terminal
Clamping connection capacity	3 x 1.5 mm ²

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.