



### Main

Range of product	Series 4
Product brand	Clipsal

### Complementary

Product or component type	Switch disconnecter
[Ue] rated operational voltage	<= 415 V AC
[In] rated current	40 A
Number of poles	1
Mounting support	DIN rail
Marking	NIGHT-OFF-DAY

### Environment

IP degree of protection	Front face: IP20
-------------------------	------------------

### Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.