



### Main

Range	Clipsal - 56 Series
Range of product	Series 56
Product brand	Clipsal
Product or component type	Plug
Device application	Power supply




### Complementary

[In] rated current	15 A
[Ue] rated operational voltage	32 V DC conforming to EN 60309-2
Colour	Orange (RAL 2004)
Material	Plastic
Plug, socket category	Low voltage
Material	Polycarbonate: housing
Outlet standard	Industrial
Connections - terminals	Screw terminal 1.5 mm <sup>2</sup>
Wire stripping length	35 Mm 10 mm
Contacts material	Pins: brass
Cable entry	Cable gland
Thread type	M20
Plug, socket, control station shape	Straight
Quality labels	RCM
Pin arrangement	E
Net weight	0.12 kg
Height	67 mm
Width	67 mm
Depth	112.5 mm
Targeted country	Australia

### Environment

Standards	AS/NZS 3112
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>

---

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

---