



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Cover: orange
Handle colour	Red
Suitability for isolation	Yes

### Complementary

Switch function	3-pole
Poles description	3P
Control type	Rotary knob
Number of poles	3
Device mounting	Surface
Fixing mode	By screws
Connections - terminals	Screw terminal cable(s) 1.5...16 mm <sup>2</sup> solid
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	63 A
Breaking capacity	63 kA
Motor M-rating AS3133	M320 at 690 V
Rotary handle padlocking	2 padlocks 8 mm
Marking	Without marking
Height	204 mm
Width	101 mm
Depth	172 mm
Net weight	1.217 kg
Targeted country	Australia

### Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations