



## Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Cover: grey
Handle colour	Grey
Suitability for isolation	No

## Complementary

Switch function	2-pole
Poles description	2P
Control type	Rotary knob
Number of poles	2
Device mounting	Surface
Connections - terminals	Screw terminal cable(s) 2.5...4 mm <sup>2</sup> solid
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	16 A
Rotary handle padlocking	2 padlocks 8 mm
Marking	Without marking
Height	107 mm
Width	101 mm
Net weight	0.32 kg
Targeted country	Australia

## Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

## Offer Sustainability

EU RoHS Directive	Will be compliant – Date to be confirmed
-------------------	--