



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Colour	Grey (RAL 7035)
Cover type	Transparent

Complementary

Number of gangs	1 gang
Shape	Rectangular
Mounting mode	Wall-mounted
Material	PVC (polyvinyl chloride): housing
Fixing mode	By screws
Number of mounting holes	4
Cable entry	1 cut-out diameter: 25 mm 1 cut-out diameter: 20 mm
Length	165 mm
Width	101 mm
Depth	165 mm
Height	101 mm
Net weight	0.6 kg
IP degree of protection	IP66 conforming to AS 60529
Standards	AS 3100

Environment

Ambient air temperature for operation	-25...75 °C
---------------------------------------	-------------

Offer Sustainability

EU RoHS Directive	Will be compliant – Date to be confirmed
Circularity Profile	No need of specific recycling operations