



Main

Range of product	600 Series
Product or component type	Illuminated module

Complementary

Material	PC (polycarbonate)
Light source colour	Green
Colour tint	White
Surface finish	Opaque
Installation direction	Vertical
Length	23 mm
Width	23 mm
Depth	25 mm
[Ue] rated operational voltage	12 V
Network type	AC/DC
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Front
Number of terminals	3
Cut-out dimensions	25 mm
Quantity per set	Set of 20
Type of packing	Crate

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.