



### Main

Range	Firetek
Product brand	Clipsal
Product or component type	Mounting base
Device application	Mounting

### Complementary

[Us] rated supply voltage	220...240 V AC 50 Hz
[Ie] rated operational current	60 mA maximum
Backup type	Battery
Battery type	Sealed rechargeable
Battery life	10 year(s)
Transmission frequency	433.42 MHz
Maximum number of device interconnected	40 for wireless alarm 40 for wired alarm wired over <= 150 m
RF range	30 m indoor use line of sight 100 m in free field
Remote control type	Dry contact momentary switch for test/hush function with max. cable length 20 m
Time delay range	2 min (pairing)
Connections - terminals	For line: screw terminal with 2 x 1.5 mm <sup>2</sup> wiring capacity For neutral: screw terminal with 2 x 1.5 mm <sup>2</sup> wiring capacity For earth loop: screw terminal with 2 x 1.5 mm <sup>2</sup> wiring capacity For interconnect: screw terminal with 2 x 1.5 mm <sup>2</sup> wiring capacity For TEST: screw terminal with 2 x 1.5 mm <sup>2</sup> wiring capacity For hush: screw terminal with 2 x 1.5 mm <sup>2</sup> wiring capacity For common: screw terminal with 2 x 1.5 mm <sup>2</sup> wiring capacity
Local signalling	Flashing: 1 LED (red) 10 s for low battery
Type of installation	Indoor
Fixing center	84 mm
Diameter	140 mm

### Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	5...95 %
Product certifications	Activfire RCM
Standards	AS/NZS 60065 AS/NZS 60950.1 AS/NZS 4268

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>