



### Main

Range	Acti 9
Product name	Acti 9 iSW
Product or component type	Switch disconnecter
Device short name	iSW
Device application	Control Isolation
Poles description	3P
Utilisation category	AC-22A
Suitability for isolation	Yes

### Complementary

[Ie] rated operational current	63 A at 415 V AC 50/60 Hz
[Ue] rated operational voltage	415 V AC 50/60 Hz
[Icm] rated short-circuit making capacity	4.2 kA switch-disconnector alone
[Icw] rated short-time withstand current	1260 A
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
Control type	Toggle
Local signalling	ON/OFF indication
Contact position indicator	Yes
Mounting mode	Fixed
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top or bottom: YES
9 mm pitches	6
Height	85 mm
Width	54 mm
Depth	73 mm
Colour	White
Mechanical durability	20000 cycles
Electrical durability	15000 cycles
Connections - terminals	Tunnel type terminals (top or bottom) - $\leq 1 \times 50 \text{ mm}^2$ - rigid Tunnel type terminals (top or bottom) - $\leq 1 \times 35 \text{ mm}^2$ - flexible Tunnel type terminals (top or bottom) - $\leq 1 \times 35 \text{ mm}^2$ - flexible with ferrule
Wire stripping length	9 mm
Tightening torque	3.5 N.m

### Environment

Standards	NZS 60947-3 AS 60947-3 EN 60947-3 IEC 60947-3 BS EN 60947-3
IP degree of protection	IP20
Pollution degree	3
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------