



### Main

Range	Kaedra
Product or component type	Weatherproof enclosure
Enclosure type	Enclosure for modular device
Accessories included with enclosure	1 terminal block 22 holes 2 wiring straps 2 marking kits 1 terminal block support
Mounting plate description	Slotted

### Complementary

Enclosure mounting	Surface
9 mm pitches	24
Number of 18 mm modules per row	12
Total number of 18 mm modules	24
Number of horizontal rows	2
Electrical insulation class	Class II Double insulation
Provided equipment	2 marking kit 2 wiring strap 1 terminal block support 1 terminal block 22 holes
Type of front cover	Transparent Reversible
[In] rated current	63 A
Type of rail	DIN
Number of pre-cutouts PG ISO	17
Number of terminal blocks	1 with 22 outgoing
Locking options description	Optional keylock
Enclosure material	Self-extinguishing polymer
Width	340 mm
Height	460 mm
Depth	160 mm
Internal depth	88 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

### Environment

Standards	EN 50262 IEC 60529 IEC 670 EN 50102 IEC 60439-3
Fire resistance	750 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Environmental characteristics (UV)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013

Overvoltage category	II
Ambient air temperature for operation	-25...60 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.000 cm
Package 1 Width	35.500 cm
Package 1 Length	47.300 cm
Package 1 Weight	3.350 kg
Unit Type of Package 2	P12
Number of Units in Package 2	28
Package 2 Height	115.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	107.228 kg

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------