



Main

Range	Actassi
Product	Vertical ring
Product destination	Rack 800 mm wide
Additional features	Openable

Complementary

Number of rack unit	1U
Maximum capacity	48
Material	Metal sheet: DC01 1.2 mm Plastic part: PA66 GF20 Plastic part: PC
Colour	Dark grey (RAL 7016) Light grey (RAL 7035)
Width	0.11 M 110 mm
Height	0.40 M 40 mm
Depth	100 Mm 0.10 m

Environment

Temperature range	-10...55 °C -10...55 °C
-------------------	----------------------------

Packing Units

Unit Type of Package 1	PCE
Unit Type of Package 2	S04

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------