

## Product data sheet

### Characteristics

# A9A26924

## Acti 9 - Auxiliary contact iOF - 1 C/O - AC/DC



### Main

Range of product	Acti 9
Product or component type	OC contact
Device short name	IOF
Signal contacts composition	1 C/O
[In] rated current	1 A: 130 V DC 1.5 A: 60 V DC 2 A: 48 V DC 6 A: 24 V DC 3 A: 415 V AC - 50/60 Hz 6 A: 240 V AC - 50/60 Hz
9 mm pitches	1

### Complementary

Range compatibility	Acti 9 iSW-NA Acti 9 iC60 Acti 9 iC65 Acti 9 iC60 RCBO Acti 9 iID Acti 9 ARA Acti 9 RCA Acti 9 iDPN (China version) Acti 9 iDPN Vigi Acti 9 iSW Acti 9 iC40
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	4 kV
Mounting mode	Clip-on
Mounting support	DIN rail
Height	86 mm
Width	9 mm
Depth	73 mm
Net weight	32 g
Colour	White
Connections - terminals	Screw clamp terminal (bottom) 1 cable(s) 1...4 mm <sup>2</sup> - rigid Screw clamp terminal (bottom) 1 cable(s) 0.5...2.5 mm <sup>2</sup> - flexible Screw clamp terminal (bottom) 2 cable(s) 2.5 mm <sup>2</sup> - rigid Screw clamp terminal (bottom) 2 cable(s) 1.5 mm <sup>2</sup> - flexible with ferrule
Wire stripping length	10 mm
Tightening torque	1 N.m

### Environment

Standards	EN/IEC 60947-5-1
IP degree of protection	IP20 conforming to EN/IEC 60947-5-1
Pollution degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Package 1 Weight	0.046 kg
Package 1 Height	0.780 dm
Package 1 width	0.200 dm
Package 1 Length	0.925 dm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------