

Product data sheet

Characteristics

NSYTBS1397

ABS box IP66 IK07 RAL7035 Int.H125W80D65
Ext.H138W93D72 Opaque cover H20



Main

Range	Thalassa
Product name	Thalassa TBS
Device application	Multi-purpose
Category	Industrial box
Height	138 mm
Width	93 mm
Depth	72 mm
Internal height	125 mm
Internal width	80 mm
Internal depth	65 mm
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Quantity per set	Set of 2
Body type	One piece moulded
Type of front cover	Low plain cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

Complementary

Material	ABS (acrylonitrile butadiene-styrene)
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	TÜV
Electrical insulation class	Class II
IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK07 conforming to IEC 62262
Glow wire resistance	650 °C conforming to IEC 60695-2-11
Ambient air temperature for storage	-15...40 °C
Operating temperature	-25...60 °C
Net weight	0.22 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	9.3 cm
Package 1 Length	13.8 cm
Package 1 Weight	220 g
Unit Type of Package 2	P12
Number of Units in Package 2	696

Package 2 Height	120 cm
Package 2 Width	80 cm
Package 2 Length	136 cm
Package 2 Weight	176 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------