

Product data sheet

Characteristics

ALB45286

Altira - 1 So - 2P+E Disp. Securiz. Si Obtur. -
Leg. La Pam. Lat. - Rosu



Principale

Gama	Altira
Tip produs sau componenta	Priza
Compatibilitate gama	Cadru de fixare Cadru de fixare
Prezentare dispozitiv	Mecanism
Numar de prize	1 x 2P + E, German
Descriere priza standard	Legare la pamant laterala
Informatii suplimentare priza	Obturat Securizat rosu
Tenta de culoare	Capac rosu (RAL 3000)

Suplimentare

Destinatie produs	Rame de fixare
Compatibilitate gama	OptiLine 70 cu adaptor Altira OptiLine 46
Pozitie papuc pentru legare la pamant	Pozitie oblica la 45°
Curent nominal	16 A la 250 V c.a. 50/60 Hz
Numar de module	2 module
Mod de fixare	Clipsare
Conexiuni - borne	Borna fara surub
Capacitate conectare prin strangere	4 x 1.5...4 x 2.5 mm ² pentru rigid cablu(uri) 4 x 1.5...4 x 2.5 mm ² pentru Impletit solid cablu(uri)
Material	PC capac mecanism
Tratament de suprafata	Antibacterial
Finisaj suprafata	Satin
Standarde	SR EN 60529 EN 62262 IEC 60884-1 NF C 61-314
Inaltime	45 mm
Latime	45 mm
Adancime	39 mm
Greutate produs	0,032 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mediu

Temperatura ambienta pentru utilizare	5...50 °C
Temperatura de depozitare	-15...60 °C
Grad de protectie IK	IK02
Grad de protectie IP	IP20
Caracteristica de mediu	Decolorant Hidrogen peroxid (H2O2) Rezistent UV Ulei Fluid de curățare a geamurilor Alcool Benzină Amoniac Acetonă Săpun lichid
Protectia mediului si probleme	Fara halogen

Unitati de impachetare

Greutatea formei de impachetare 1	0,035 kg
Inaltimea formei de impachetare 1	0,400 dm
Latimea formei de impachetare 1	0,450 dm
Lungimea formei de impachetare 1	0,450 dm

Durabilitatea ofertei

Stare ofertă sustenabilă	Produs Green Premium
Directiva RoHS UE	Conform Declaratia RoHS UE
Fara mercur	Da
Informatii privind scutirea de la RoHS	Da
Regulamentul RoHS China	Declaratia RoHS China
Raport de mediu	Profilul Ambiental Al Produsului

Garantie contractuală

Garantie	18 months
----------	-----------