

Product data sheet

Characteristics

LE3D35P7

Demaror Stea-Triunghi Capsulat - Tesys Le3-D
- 30 Kw - Bobina 230 V C.A.



Principale

Gama	TeSys
Nume produs	TeSys LE
Nume scurt al dispozitivului	LE3D
Tip produs sau componenta	Enclosed star-delta starter
Domeniu de utilizare al dispozitivului	Standard
Material	Policarbonat
Categorie de utilizare	AC-3
Compozitie dispozitiv	Thermal overload relay comandat separat Star-delta contactors Mechanical interlock
[Ie] curent nominal de utilizare	35 A AC-3
Putere motor kW	15 KW la 220 V c.a. 50/60 Hz 30 KW la 380/400 V c.a. 50/60 Hz 30 KW la 415 V c.a. 50/60 Hz 30 kW la 440 V c.a. 50/60 Hz
[Uc] control circuit voltage	230 V c.a. 50/60 Hz
Tip de control	Buton start verde I Buton stop/reset rosu O

Suplimentare

Conexiuni - borne	Circuit electric borne cu șurub Circuit de comanda borne cu șurub
Numarul intrarii de cablu	2 ISO20 top 2 ISO25 top 2 ISO32 top 2 ISO40 top 2 ISO20 jos 2 ISO25 jos 2 ISO32 jos 2 ISO40 jos
Latime	186 mm
Inaltime	348 mm
Adancime	175,5 mm
Greutate produs	5,16 kg

Mediu

Grad de protectie IP	IP65 conformitate cu SR EN 60529
Grad de protectie IK	IK07 conformitate cu SR EN 60529
Standarde	IEC 60947-4-1
Temperatura ambientala de utilizare	-5...40 °C
Caracteristica de mediu	Mediu standard

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Unitati de impachetare

Tip unitate a formei de impachetare 1	PCE
Numar de unitati in forma de impachetare 1	1
Greutatea formei de impachetare 1	5,16 kg
Inaltimea formei de impachetare 1	26 cm
Latimea formei de impachetare 1	29 cm
Lungimea formei de impachetare 1	40 cm

Durabilitatea ofertei

Stare ofertă sustenabilă	Produs Green Premium
Regulamentul REACH	Declaratia REACH
Conform REACH fara SVHC	Da
Directiva RoHS UE	Conform Declaratia RoHS UE
Fara metale grele toxice	Da
Fara mercur	Da
Informatii privind scutirea de la RoHS	Da
Regulamentul RoHS China	Declaratia RoHS China
Raport de mediu	Profilul Ambiental Al Produsului
WEEE	În Uniunea Europeana, produsele trebuie reciclate respectand sistemul specific de colectare a deseurilor si nu trebuie sa ajunga in pubelele de colectare a deseurilor menajere.

Garanție contractuală

Garantie	18 months
----------	-----------