

Product data sheet

Characteristics

NSYPAPLA105

internal door for PLA enclosure H1000xW500 mm



Principale

Gama	Thalassa
Categorie de accesorii/ piese separate	Accesoriu de dulap
Tip produs sau componenta	Ușă
Application	Multifuncțional
For enclosure nominal dimensions	-
Locatie de montare	Partea frontala
Compatibilitate gama	Thalassa PLA
Compozitie dispozitiv	1 ușă Elemente de fixare M8 brass inserts

Suplimentare

Material	aluminiu
Culoare	Gri (RAL 7032)
Tip incuietoare	Lock 5 mm double bar
Numar de incuietori	2
Tip usa	Internal plain
Deschidere usa	Stanga (110 °)
Inaltime	898 mm
Adancime	398 mm
Adancime	Available depth between enclosure door 30 mm

Unitati de impachetare

Greutatea formei de impachetare 1	3,441 kg
Inaltimea formei de impachetare 1	35,000 mm
Latimea formei de impachetare 1	415,000 mm
Lungimea formei de impachetare 1	905,000 mm

Garantie contractuală

Garantie	18 months
----------	-----------