

Product data sheet

Characteristics

NSYPAPLA157

internal door for PLA enclosure H1500xW750 mm



Principale

Gama	Thalassa
Categorie de accesorii/piese separate	Accesorii de dulap
Tip produs sau componenta	Ușă
Application	Multifuncțional
For enclosure nominal dimensions	-
Locatie de montare	Partea frontala
Compatibilitate gama	Thalassa PLA
Compozitie dispozitiv	1 ușă Elemente de fixare M8 brass inserts

Suplimentare

Material	aluminiu
Culoare	Gri (RAL 7032)
Tip incuietoare	Lock 5 mm double bar
Numar de incuietori	2
Tip usa	Internal plain
Deschidere usa	Stanga (110 °)
Inaltime	1398 mm
Adancime	648 mm
Adancime	Available depth between enclosure door 30 mm

Unitati de impachetare

Greutatea formei de impachetare 1	8,000 kg
Inaltimea formei de impachetare 1	40,000 mm
Latimea formei de impachetare 1	1410,000 mm
Lungimea formei de impachetare 1	660,000 mm

Garantie contractuală

Garantie	18 luni
----------	---------