

Product data sheet

Characteristics

NSYPCV2D168

Spacial Sf/Sm Usa Dubla Ventilata - 1600X800 Mm



Principal

Gama	Spacial
Categorii accesorii / piese de schimb	Accesorii cofret
Tip produs sau componenta	19" door
Aplicatie	Multifuncțional
Pentru dimensiunile nominale ale carcasei	-
Locul de montare	Fata
Compatibilitate gama	Spacial (Spacial SF) Spacial (Spacial SM)
Compozitie dispozitiv	1 încuietoare cu mâner □i inser□ie cu bară dublă de 5 mm 1 sistem bară de blocare in 4 puncte 2 ușă 1 sistem de blocare
Cantitate pe set	Set de 1

Suplimentar

Material	Tabla de otel
Culoare	Gri (RAL 7035)
Finisare suprafata	Pudră epoxy-poliester
Tip incuietoare	Blocare 5mm bara dubla
Numar de incuietori	1
Tip usa	Ventilated
Parte de deschidere usa	Reversibil (120 °)
Inaltime	Nominal:1600 mm
Latime	Nominal 800 mm

Garanție contractuală

Garantie	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.