

Product data sheet

Characteristics

NSYBCE8

Spacial SF brush flexible cable entry gaskets -
25 mm - 800 mm enclosure



Main

Range	Spacial
Product or component type	Brush gasket
Accessory / separate part category	Cable management accessory
Device application	Multi-purpose
Range compatibility	Spacial Spacial SF suitable enclosure
Device composition	2 gasket
Quantity per set	Set of 1



Complementary




Mounting support	Cable gland plate
Cable entry	1 or 2 entries
Fixing mode	Clipped
Height	70 mm
Width	800 Mm nominal: 735 mm real:
Depth	25 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	8.0 cm
Package 1 Length	74.0 cm
Package 1 Weight	426.0 g
Unit Type of Package 2	P12
Number of Units in Package 2	120
Package 2 Height	105.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	92.2 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Logistical informations

Country of origin	FR
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------