



## Main

Range	Exiway
Product name	Exiway One
Product or component type	Emergency luminaire
Function	Self-test
Operational mode	Maintained
Number of batteries	1 x 6 V 1.5 Ah Ni-Cd (Nickel-Cadmium)
Light source	Fluorescent tube G5 8 W
Wiring device additional information	Can be inhibited with rest mode via Teleur range of remote controls

## Complementary

Range compatibility	TBS remote control
[Ue] rated operational voltage	230 V 50 Hz
Power consumption in VA	18.6 VA
Power consumption in W	7.2 W
Electrical insulation class	Class II
Autonomy	1 h
Charging time	12 h
Type of glass	Fresnel glass
Device mounting	Surface ceiling Hanging ceiling Flush false ceiling Flush wall Surface wall Electrified track
Height	160 mm
Depth	68 mm
Width	375 mm






## Environment

IP degree of protection	IP65
IK degree of protection	IK07
Fire resistance	850 °C
Product certifications	ENEC
Ambient air temperature for operation	0...40 °C
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	16.4 cm
Package 1 Length	38.1 cm
Package 1 Weight	1.22 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#"> EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------