



Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	336 mm outside:
Height	600 mm
Depth	143 mm
Nb of 18 mm modules per row	13
Nb of horizontal rows	3
Electrical insulation class	Class II Double insulation
Provided equipment	1 x identification label 1 x marking kit 1 x terminal block 1 x blanking plate strip
Type of door	Without

Complementary

Enclosure mounting	Surface
9 mm pitches	26
Total number of 18 mm modules	39
Power dissipation in W	45 W
[In] rated current	90 A
Type of rail	DIN
Cable entry	Trunking Cable or tube Removable plates Cut-out plates
Comb busbar and distribution block compatibility	XE compatible
Number of terminal blocks	1 earth (Quick) with 24 outgoers
Distribution block outgoers	3 x 25 mm ² for earth 21 x 4 mm ² for earth
Enclosure material	Back part: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004)
Targeted country	Belgium

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.






Environment

Fire resistance	Back part: 750 °C Front face: 750 °C
IP degree of protection	IP30 without door IP40 with door
IK degree of protection	IK08 without door IK09 with door
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.9 cm
Package 1 Width	42.2 cm
Package 1 Length	66.4 cm
Package 1 Weight	3.9 kg
Unit Type of Package 2	P12
Number of Units in Package 2	21
Package 2 Height	120.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	93.9 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations