



Main

Range of product	CANopen
Bus type	CANopen
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Accessory / separate part destination	CANopen bus
Cable length	300 m

Complementary

Marking	CE
Net weight	21.87 kg

Environment

Product certifications	UL
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	33.500 cm
Package 1 Width	40.000 cm
Package 1 Length	40.000 cm
Package 1 Weight	21.870 kg
Unit Type of Package 2	P12
Number of Units in Package 2	18
Package 2 Height	113.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	405.660 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations Circularity Profile

Contractual warranty

Warranty	18 months
----------	-----------