



### Main

Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Poles description	3P
Number of ways	16 ways 3 L with 18 mm pitch
Distance between way	54 mm
Poles distribution	L1 L2 L3
Connector type	Tooth
Length in 18 mm modules	24

### Complementary

[In] rated current	Double feed 100 A ( 40 °C ) Single feed 80 A ( 40 °C )
[Ui] rated insulation voltage	500 V conforming to IEC 664
Mounting mode	Horizontal
9 mm pitches	48

### Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.