



Main

Range	PowerLogic
Device short name	VLT
Product or component type	Voltmeter
Range compatibility	Prisma P door Prisma G door
Scale	0-500 V
Technology type	Ferromagnetic
Scale type	80 mm over 90°
Mounting support	Front face

Complementary

Type of measurement	Voltage
Accuracy class	Class 1.5
Power consumption in VA	3 VA
Power consumption in VA	3 VA
Overload withstand	1.2 Un, permanently 2 Un, 5 s
Device mounting	Flush
Operating position	30°/vertical
Width	96 mm
Height	96 mm
Maksimalna dubina	75 mm
Temperature drift	+/- 0.003 %/°C

Environment

Standards	IEC 61000-4 IEC 60051-1 IEC 61010-1
IP degree of protection	IP52
Ambient air temperature for operation	-25...50 °C
Reference temperature	23 °C

Broj pakirnih jedinica

Vrsta pakirne jedinice Paketa 1	PCE
Broj pakirnih jedinica u Paketu 1	1
Paket 1 Težina	282 g
Paket 1 Visina	10,5 cm
Paket 1 Širina	11 cm
Paket 1 Duljina	11,5 cm
Vrsta pakirne jedinice Paketa 2	S03
Broj pakirnih jedinica u Paketu 2	12
Paket 2 Težina	3,83 kg
Paket 2 Visina	30 cm
Paket 2 Širina	30 cm
Paket 2 Duljina	40 cm

Offer Sustainability

Direktiva EU RoHS	Sukladno Izjava EU RoHS
Propis RoHS za Kinu	Izjava RoHS Za Kinu
Izjava o očuvanju okoliša	Ekološki Profil Proizvoda
Profil cirkularnosti	Informacije O Kraju Vijeka Trajanja
WEEE	Proizvod se na tržištima EU mora odlagati u skladu sa specifičnim propisima o prikupljanju otpada; nikako se ne smije odlagati s komunalnim otpadom.

Contractual warranty

Jamstvo	18 months
---------	-----------