



Main

Range of product	Acti9
Product name	Acti9 iRO
Product or component type	Buzzer
Device short name	iRO

Complementary

[Us] rated supply voltage	230 V AC at 50/60 Hz
Power consumption in VA	5 VA
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	2
Height	81 mm
Width	18 mm
Depth	72 mm
Net weight	64 g
Colour	White
Auxiliary connection terminal	Tunnel type terminalsrigid 4 mm ² Tunnel type terminalsflexible 4 mm ² Tunnel type terminalsflexible with ferrule 4 mm ²
Wire stripping length	12 mm for bottom connection
Tightening torque	1.3 N.m

Environment

Noise level	70 dB
Type of sound	Buzzer
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Ambient air temperature for operation	-10...40 °C
Ambient air temperature for storage	-25...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	6.6 cm
Package 1 Length	8.2 cm
Package 1 Weight	55.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8.3 cm
Package 2 Width	10.0 cm

Package 2 Length	22.8 cm
Package 2 Weight	715.0 g
Unit Type of Package 3	S03
Number of Units in Package 3	144
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	9.115 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------