



Main

Range of product	Acti 9
Product name	Acti 9 iRO
Product or component type	Buzzer
Device short name	IRO

Complementary

[Us] rated supply voltage	230 V AC at 50/60 Hz
Power consumption in VA	5 VA
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	2
Height	81 mm
Width	18 mm
Depth	72 mm
Net weight	64 g
Colour	White
Auxiliary connection terminal	Tunnel type terminalsrigid 4 mm ² Tunnel type terminalsflexible 4 mm ² Tunnel type terminalsflexible with ferrule 4 mm ²
Wire stripping length	12 mm for bottom connection
Tightening torque	1.3 N.m

Environment

Noise level	70 dB
Type of sound	Buzzer
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Ambient air temperature for operation	-10...40 °C
Ambient air temperature for storage	-25...60 °C

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------