



Main

Range name	Anya
Function	TV-SAT ending outlet
Delivery form	Complete product
TV socket type	End-of-line (terminal socket)
Attenuation	1 dB
Cover plate color	White
Cover frame color	White
Kind of terminals	Screw terminals

Complementary

Installation	Flush
TV connector type	Male IEC 9.52 mm
SAT connector type	F type
Path attenuation	1 DB TV/UHF signal470...830 MHz 13 DB SAT signal950...2400 MHz 2.2 dB TV/VHF signal118...470 MHz
DC current flow	In SAT socket
Number per line	4
Material of visible parts	ABS (acrylonitrile butadiene-styrene): central plate ABS (acrylonitrile butadiene-styrene): cover frame
Surface finish	Gloss
Height	81.5 mm
Width	81.5 mm
Depth	40 mm
Depth of visual part	11 mm
Net weight	0.122 kg

Environment

IP degree of protection	IP20
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration