



### Main

Range	Asfora
Product or component type	Data socket
Device application	Communication
Device presentation	Complete product
Cable shielding type	UTP
Data socket type	RJ45
Colour tint	White
Type of packing	Flow-pack

### Complementary

Device mounting	Flush
Socket number	1
Communication network category	5e
Connections - terminals	IDC
Number of cables	1
Cable stiffness	Rigid
Material	ABS (acrylonitrile butadiene-styrene) central plate ABS (acrylonitrile butadiene-styrene) cover frame
Surface finish	Glossy
Conductor material	Copper
Fixing mode	Claws 51...80 mm
Height	83 mm
Width	83 mm
Maksimalna dubina	48 mm
Projecting depth	9 mm
Net weight	0,063 kg

### Environment

IP degree of protection	IP20
-------------------------	------

### Broj pakirnih jedinica

Paket 1 Težina	63,000 g
Paket 1 Visina	110,000 mm
Paket 1 Širina	160,000 mm
Paket 1 Duljina	50,000 mm

## Offer Sustainability

Direktiva EU RoHS	Sukladno <a href="#">Izjava EU RoHS</a>
Bez otrovnih teških metala	Da
Bez žive	Da
Informacije o RoHS izuzeću	<a href="#">Da</a>
Propis RoHS za Kinu	<a href="#">Izjava RoHS Za Kinu</a>
WEEE	Proizvod se na tržištima EU mora odlagati u skladu sa specifičnim propisima o prikupljanju otpada; nikako se ne smije odlagati s komunalnim otpadom.

## Contractual warranty

Jamstvo	18 months
---------	-----------