



Main

Range	TeSys
Product or component type	Electrical remote stop
Device short name	LAD
Accessory / separate part category	Electrical accessory
Product compatibility	LRD313...LRD365 LRD01...35 LR3D01...D35 LR3D313...LR3D365
[Uc] control circuit voltage	415/440 V AC 50/60 Hz


Complementary

Maximum inrush power in VA	100 VA
Net weight	0.09 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	105 g
Package 1 Height	5.1 cm
Package 1 width	4.9 cm
Package 1 Length	4.9 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------