



Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Top
Number of modules	6 modules
Fixing mode	Clip-in
Cover frame colour tint	Glossy chrome
Decoration colour	Graphite

Complementary

Material	ASA + PC: decorative frame ASA + PC: intermediate part Zamak: cover frame
Standards	EN 60669-1
Height	12 mm
Width	200 mm
Depth	84 mm
Net weight	0.103 kg
Market segment	Residential Small commercial

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Liquid soap Acetone Alcohol Window-cleaning fluid Oil UV resistant Petrol Bleach

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	8.4 cm
Package 1 Length	20.0 cm
Package 1 Weight	116.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Height	5.5 cm
Package 2 Width	10.8 cm
Package 2 Length	24.7 cm
Package 2 Weight	409.0 g

Unit Type of Package 3	S03
Number of Units in Package 3	51
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	7.349 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------