



Main

Range	PratiKa
Product or component type	Socket
Device short name	PratiKa socket
Plug, socket category	Low voltage
Poles description	2P + E
Network type	AC
Outlet standard	Industrial

Complementary

Mounting mode	Wall-mounted
Plug, socket, control station shape	Angled
[In] rated current	16 A
[Ue] rated operational voltage	200...250 V
Network frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Housing self-extinguishing engineering polymer
Contacts material	Sleeves brass
Connections - terminals	Captive screws
Cable cross section	1...4 mm ²
Cable outer diameter	21 mm
Thread type	M25
Neto težina	0,2 kg
Maksimalna visina	129 mm
Maksimalna širina	62 mm
Maksimalna dubina	100 mm
Colour	Sivo RAL 7035)
Voltage colour	Blue

Environment

Standards	IEC 60309-2 IEC 60309-1
IP degree of protection	IP44 IEC 60529
IK degree of protection	IK08 EN 62262
Fire resistance	750 °C IEC 60695-2-1
Relative humidity	50 % 40 °C 70 % 30 °C 90 % 20 °C
Ambient air temperature for operation	35 °C 86400 s)

Offer Sustainability

Status održive ponude	Proizvod Green Premium
Uredba REACH	Izjava REACH
Direktiva EU RoHS	Proaktivna sukladnost (proizvod izvan zakonskog okvira direktive EU RoHS) Izjava EU RoHS
Bez žive	Da
Informacije o RoHS izuzeću	Da
Propis RoHS za Kinu	Izjava RoHS Za Kinu
Izjava o očuvanju okoliša	Ekološki Profil Proizvoda

Contractual warranty

Jamstvo	18 months
---------	-----------