

## Product data sheet

### Characteristics

# G45ACCUN

## Exclusive - cooker control unit - 2 gangs - neon indicator lamp - white



### Main

Range of product	Exclusive
Product or component type	Cooker control unit
Device presentation	Complete product
Outlet standard	British
Colour tint	White moulded matt
Quantity per set	Set of 1



### Complementary

Rated current	45 A at 230 V AC 50 Hz
Number of gangs	2 gangs
Pilot light	Neon indicator
Fixing mode	By screws M3.5 x 30 mm
Connections - terminals	Screw terminals
Material	Urea (carbamide)
Type of installation	Indoor
Depth	36 mm
Width	146 mm
Height	86 mm
Net weight	0.26 kg

### Environment

Standards	BS EN 60669-1 BS 5733 BS 4177
IP degree of protection	IP20

### Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

### Contractual warranty

Warranty	18 months
----------	-----------