

Product data sheet

Characteristics

G45CX

Exclusive - cooker control unit - 1 gang - white



Main

Range of product	Exclusive
Product or component type	Cooker control unit
Device presentation	Complete product
Outlet standard	British
Colour tint	White moulded matt
Quantity per set	Set of 10

Complementary

Rated current	45 A at 230 V AC 50 Hz
Number of gangs	1 gang
Pilot light	Without neon indicator
Fixing mode	By screws M3.5 x 30 mm
Connections - terminals	Screw terminals
Material	Urea (carbamide)
Type of installation	Indoor
Depth	36 mm
Width	86 mm
Height	86 mm
Net weight	0.16 kg

Environment

Standards	BS EN 60669-1 BS 4177 BS 5733
IP degree of protection	IP20

Packing Units

Package 1 Weight	0.160 kg
Package 1 Height	8.500 cm
Package 1 width	8.500 cm
Package 1 Length	3.500 cm

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty

18 months
