

## Product data sheet

### Characteristics

# GSKTSW3G

Exclusive Square edge white moulded - switched and fused socket - 13 A - 230 V



### Main

Range of product	Exclusive
Aesthetic name	Square edge white moulded
Product or component type	Switched and fused socket
Device presentation	Complete product
Outlet standard	British
Colour tint	White matt
Quantity per set	Set of 5



### Complementary

Switch function	1-pole
Rated current	13 A at 230 V AC 50 Hz
Actuator	Rocker
Number of gangs	3 gangs
Pilot light	Without neon indicator
Fixing mode	By screws
Connections - terminals	Screw terminals
Material	Urea (carbamide)
Type of installation	Indoor
Depth	31 mm
Width	205 mm
Height	86 mm
Net weight	0.332 kg

### Environment

Standards	BS 1363
IP degree of protection	IP20

### Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

### Contractual warranty

Warranty	18 months
----------	-----------