

Product data sheet

Characteristics

GSWDP20AFO

Exclusive - 2-pole switch with flex outlet - 1 gang - 20 AX - white



Main

Product or component type	Switch with flex outlet
Device presentation	Complete product
Colour tint	White
Quantity per set	Set of 10

Complementary

Switch function	2-pole
Control type	Rocker
Number of gangs	1 gang
Pilot light	Without neon indicator
Device mounting	Wall mounted
Rated current	20 AX at 230 V AC
Connections - terminals	Screw terminals
Material	Urea (carbamide)
Surface finish	Matt
Height	86 mm
Width	86 mm
Depth	31 mm
Net weight	0.113 kg

Environment

Standards	BS EN 60669-1
IP degree of protection	IP20

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------