

Product data sheet

Characteristics

82127

PratiKa industrial socket - 32 A - 2P - 20...25 V DC - IP44



Principal

Gama	PratiKa
Tip produs sau componenta	Priza
Nume scurt al dispozitivului	PratiKa socket
Plug, socket category	Extra-low voltage
Descriere poli	2P
Tip retea electrica	C.c.
Standard priza	Industrial

Suplimentar

Mod de montare	Montaj pe perete
Forma fisa, priza, carcasa	Angled
[In] calibru	32 A
[Ue] tensiune nominala	40...50 V 20...25 V
Secondary keyway clockwise position	10 h
Plug, socket material	Carcasa self-extinguishing engineering polymer
Materialul contactelor	Pins stainless steel Sleeves nickel plated brass Springs stainless steel
Conexiuni - borne	Captive screws, completely loosened
Sectiune cablu	4...10 mm ²
Diametru exterior cablu	6...23 mm
Intrare cablu	Fair lead
Tip filet	Pg 21
Greutate neta	0,199 kg
Dimensiune baza	70 x 82 mm
Inaltime	118 mm
Latime	70 mm
Adancime	81 mm
Culoare	Gri (RAL 7035)
Voltage colour	White

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mediu

Standarde	EN 60309-2 EN 60309-1
Grad de protecție IP	IP44 conformitate cu SR EN 60529
Grad de protecție IK	IK08 conforming to EN 62262
Rezistența la foc	850 °C conformitate cu IEC 60695-2-11
Umiditate relativă	50 % la 40 °C 70 % la 30 °C 90 % la 20 °C
Temperatura ambientală de utilizare	35 °C 86400 s)

Unitati de ambalare

Unitate de masura pentru prima forma de impachetare	PCE
Numar unitati in prima forma de impachetare	1
Inaltime prima forma de impachetare	8,1 cm
Latime prima forma de impachetare	7 cm
Lungime prima forma de impachetare	11,8 cm
Greutate prima forma de impachetare	190 g

Sustenabilitatea ofertei

Stare ofertă sustenabilă	Produs Green Premium
Regulamentul REACH	 Declaratia REACH
Directiva RoHS UE	Conformitate proactivă (Produs în afara domeniului de aplicare a EU RoHS)
Fara mercur	Da
Regulamentul RoHS China	 Declaratia RoHS China
Informatii privind scutirea de la RoHS	 Da
Profil circularitate	Nu sunt necesare operatii de reciclare speciale