

Product data sheet

Characteristics

LC4D25AF7

demaror DOL pe placă de montare - TeSys
LC4-D - 25 A - bobină 110 V c.a.



Principal

Gama de produse	TeSys
Nume scurt al dispozitivului	LC4
Tip produs sau componenta	Demaror DOL
Putere motor kW	11 KW la 380...400 V c.a. 50/60 Hz 11 KW la 415 V c.a. 50/60 Hz 11 KW la 440 V c.a. 50/60 Hz 15 KW la 500 V c.a. 50/60 Hz 5,5 kW la 220...230 V c.a. 50/60 Hz
Categorie de utilizare	AC-3
[Ue] tensiune nominala	110 V c.a. 50/60 Hz
[Ie] curent nominal	25 A

Suplimentar

Compozitie dispozitiv	Separator siguranta Contactor
Suport de montare	Placa
Latime	86 mm
Inaltime	173 mm
Adancime	98 mm
Greutate neta	1,58 kg

Garanție contractuală

Garantie	18 luni
----------	---------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.