

Product data sheet

Characteristics

DL1CJ0245

LED bulb with BA9s base - orange - 24 V AC/DC



Local distributor code: 380953738
EAN Code: 3389110660005



Main

| | |
|---------------------------------------|-------------------------|
| Range compatibility | Harmony XB4 |
| Accessory / separate part type | LED bulb |
| Accessory / separate part category | Lighting accessory |
| Accessory / separate part destination | Illuminated push-button |
| [Us] rated supply voltage | 24 V AC/DC |
| Signalling colour | Orange |
| Sale per indivisible quantity | 1 |
| Product or component type | LED bulb |

Complementary

| | |
|------------|----------|
| Bulb base | BA 9s |
| Net weight | 0.002 kg |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.0 cm |
| Package 1 Width | 1.0 cm |
| Package 1 Length | 2.5 cm |
| Package 1 Weight | 2.0 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 3.5 cm |
| Package 2 Width | 10.5 cm |
| Package 2 Length | 4.5 cm |
| Package 2 Weight | 30.0 g |
| Unit Type of Package 3 | S01 |
| Number of Units in Package 3 | 300 |
| Package 3 Height | 15.0 cm |
| Package 3 Width | 15.0 cm |
| Package 3 Length | 40.0 cm |
| Package 3 Weight | 1.135 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|