

Product data sheet

Characteristics

GS2AH220

External rotary handle, TeSys GS, red handle, right side mounting, 2 positions I-O, IP65, for GS 32-63A IEC



Local distributor code: 393394999
EAN Code: 3389119411707



Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AH
Product or component type	Rotary handle
Range compatibility	TeSys TeSys GS GS1D[RETURN]TeSys TeSys GS GS2F[RETURN]TeSys TeSys GS GS2G[RETURN]FuPact FuPactT GS GSB32[RETURN]FuPact FuPactT GS GSC50
Type of operating handle	External right side
Handle colour	Red
Handle front plate colour	Yellow

Complementary

Handle positions	O-I
Rotary handle padlocking	Lockable in O position
Switch rated current	32 A 50 A 63 A
Standards	IEC
Net weight	0.2 kg

Environment

IP degree of protection	IP65
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	15 cm
Package 1 Length	15 cm
Package 1 Weight	199 g
Unit Type of Package 2	S03
Number of Units in Package 2	25
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5.56 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------