

# Product data sheet

## Characteristics

# GS2AH330

External rotary handle, TeSys GS, black handle, left side mounting, 2 positions I-O, IP65, for GS 100-400A IEC



Local distributor code: 393395079  
EAN Code: 3389119411776



## Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AH
Product or component type	Rotary handle
Range compatibility	TeSys TeSys GS GS2J TeSys TeSys GS GS2K TeSys TeSys GS GS2L TeSys TeSys GS GS2N TeSys TeSys GS GS2P TeSys TeSys GS GS2Q
Type of operating handle	External left side
Handle colour	Black
Handle front plate colour	Grey

## Complementary

Handle positions	O-I
Rotary handle padlocking	Lockable in O position
Switch rated current	100 A 125 A 160 A 200 A 250 A 315 A 400 A
Standards	IEC
Net weight	0.24 kg

## Environment

IP degree of protection	IP65
-------------------------	------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	13.500 cm
Package 1 Length	17.500 cm
Package 1 Weight	390.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	14
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm

Package 2 Length	40.000 cm
Package 2 Weight	6.313 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

### Contractual warranty

Warranty	18 months
----------	-----------