

# Product data sheet

## Characteristics

# GV3PC01

TeSys GV3 - Enclosure for TeSys GV3P/L -  
black handle - IP65



Local distributor code: 398237048  
EAN Code: 3389119409933



## Main

|                                    |                    |
|------------------------------------|--------------------|
| Range                              | TeSys              |
| Product or component type          | Enclosure          |
| Device short name                  | GV3PC              |
| Accessory / separate part category | Mounting accessory |
| Product compatibility              | GV3P<br>GV3L       |
| Enclosure type                     | Surface mounting   |

## Complementary

|                          |                                                   |
|--------------------------|---------------------------------------------------|
| Material                 | Metal                                             |
| Rotary handle padlocking | Padlock in ON position<br>Padlock in OFF position |
| Handle colour            | Black                                             |
| Height                   | 312 mm                                            |
| Width                    | 181 mm                                            |
| Depth                    | 203.5 mm                                          |
| Net weight               | 2 kg                                              |

## Environment

|                         |      |
|-------------------------|------|
| IP degree of protection | IP65 |
| Product certifications  | UKCA |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 19.5 cm  |
| Package 1 Width              | 21.5 cm  |
| Package 1 Length             | 31.5 cm  |
| Package 1 Weight             | 3.642 kg |
| Unit Type of Package 2       | PAM      |
| Number of Units in Package 2 | 60       |
| Package 2 Height             | 94.5 cm  |
| Package 2 Width              | 100 cm   |
| Package 2 Length             | 120 cm   |
| Package 2 Weight             | 231 kg   |

## Offer Sustainability

|                            |                                                                                                                                 |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                           |
| REACH Regulation           |  <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant  <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes                                                                                                                             |
| Mercury free               | Yes                                                                                                                             |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information |  <a href="#">Yes</a>                           |
| Circularity Profile        | No need of specific recycling operations                                                                                        |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins     |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|