

Product data sheet

Characteristics

LA7D03M

TeSys D thermal overload relays - remote electrical tripping - 220...230 V DC/AC

Local distributor code: 2210885

EAN Code: 3389110055139



Main

Range	TeSys
Product or component type	Electrical remote tripping
Device short name	LA7D
Accessory / separate part category	Electrical accessory
Product compatibility	LR2D LR3D35.. LRD15.. LRD33.. LR3D33.. LR3D43.. LRD43.. LR3D15..
[Uc] control circuit voltage	220/230 V AC 50/60 Hz 220/230 V DC




Complementary


Maximum inrush power in VA	100 VA
Inrush power in W	0...100 W
Net weight	0.09 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	4.8 cm
Package 1 Length	4.8 cm
Package 1 Weight	106.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	32
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.565 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Contractual warranty	
Warranty	18 months