

## Product data sheet

### Characteristics

# NSYCRS50W120V

Climasys Ultra thin resistance heater low starting current 50W 120V 200x320mm



Local distributor code: 400815853  
EAN Code: 3606480530159



### Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Ultra thin resistance heater
Power range	50 W
Input voltage	120 V AC 50/60 Hz
Electrical connection	Cable length: 2 m

### Complementary

Operating position	Vertical Horizontal
Ambient air temperature for operation	-60...70 °C
Temperature setting range	-40...70 °C
Material	Silicone rubber
Height	200 mm external:
Width	320 mm external:
Depth	1.6 mm external:
Device composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts Fixing accessories
Condition of use	Electrical protection is needed Air sealed enclosure Heaters must be installed with a thermal controller
Fixing mode	By 4 screws
Mounting support	DIN rail Standard mounting plate Telequick mounting plate Adhesive Velcro

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------