

## Product data sheet

### Characteristics

## VW3A8306D30

cable for Modbus serial link - 1 x RJ45 and free wires at other end - cable 3 m

Local distributor code: 386307223

EAN Code: 3389110269468



### Main

|                                       |   |
|---------------------------------------|---|
| Accessory / separate part category    | Connection accessories  |
| Accessory / separate part type        | Connecting cable  |
| Accessory / separate part designation | Cable for Modbus serial link  |
| Accessory / separate part destination | Ethernet network<br>XBTGT terminal<br>Modbus bus serial line<br>Soft stop unit<br>Twido PC programming terminal |
| Range compatibility                   | TeSys U<br>Harmony XBT<br>Twido<br>Advantys OTB<br>Lexium SD3<br>Altistart<br>Altivar                           |
| Cable length                          | 3 m   |
| Electrical connection                 | 1 male connector RJ45<br>Free end   |

### Complementary

|            |         |
|------------|---------|
| Net weight | 0.15 kg |
|------------|---------|

### Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 3.000 cm  |
| Package 1 Width              | 13.000 cm |
| Package 1 Length             | 13.000 cm |
| Package 1 Weight             | 103.000 g |
| Unit Type of Package 2       | S03       |
| Number of Units in Package 2 | 40        |
| Package 2 Height             | 30.000 cm |
| Package 2 Width              | 30.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 4.750 kg  |
| Unit Type of Package 3       | P06       |
| Number of Units in Package 3 | 320       |
| Package 3 Height             | 75.000 cm |
| Package 3 Width              | 60.000 cm |
| Package 3 Length             | 80.000 cm |
| Package 3 Weight             | 47.484 kg |

Offer Sustainability

|                       |  |
|-----------------------|--|
| REACH Regulation      | <a href="#">📄 REACH Declaration</a>  |
| REACH free of SVHC    | Yes  |
| EU RoHS Directive     | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">📄 EU RoHS Declaration</a> |
| China RoHS Regulation | <a href="#">📄 China RoHS Declaration</a>   |

Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|